# Professional heating technology for industry and laboratory applications



## **Mounting brackets**



#### series HM-MS 1

suitable for connection box HM-PCB1

bracket complete for tube mounting, consisting of:

- 1 pc. mounting plate made in V2A
- 2 pc. angle made in V2A
- 4 pc. mounting screws with nuts and washers for the mounting of the connecting box
- 2 pc. 0,8m thread-clambing band
- 2 pc. thread clamping head
- 2 pc. deflection angle with mounting screws
- 2 pc. screw M8x8 with helical spring washers
- 4 pc. nut M6 with washers and helical spring washers

order-no.: 72000010

### series HM-MS2

suitable for connection box HM-PCB2

bracket complete for tube mounting, consisting of:

- 1 pc. mounting plate made in V2A
- 2 pc. angle made in V2A
- 4 pc. mounting screws with nuts and washers for the mounting of the connecting box
- 2 pc. 0,8m thread-clambing band
- 2 pc. thread clamping head
- 2 pc. deflection angle with mounting screws
- 2 pc. screw M8x8 with helical spring washers
- 4 pc. nut M6 with washers and helical spring washers

order-no.: 72000011

#### series HM-MS3

suitable for connection box HM-PCB 3

bracket complete for tube mounting, consisting of:

- 1 pc. mounting plate made in V2A
- 2 pc. angle made in V2A
- 4 pc. mounting screws with nuts and washers for the mounting of the connecting box
- 2 pc. 0,8m thread-clambing band
- 2 pc. thread clamping head
- 2 pc. deflection angle with mounting screws
- 2 pc. screw M8x8 with helical spring washers
- 4 pc. nut M6 with washers and helical spring washers


order-no.: 72000012



suitable for capillary thermostat HM-CSTL

bracket complete for tube mounting, consisting of:

- 1 pc. mounting plate made in V2A
- 2 pc. angle made in V2A
- 4 pc. mounting screws with nuts and washers for the mounting of the connecting box
- 2 pc. 0,8m thread-clambing band
- 2 pc. thread clamping head
- 2 pc. deflection angle with mounting screws
- 2 pc. screw M8x8 with helical spring washers
- 4 pc. nut M6 with washers and helical spring washers









D-69181 Leimen Gottlieb-Daimler-Straße 2 Phone + 49 (0) 6224 7 10 93 + 94


info@labo-mohr.de www.labo-mohr.de + 49 (0) 6224 7 70 12




HM-MS1 stainless steel plate 120 x 120 mm



HM-MS2 stainless steel plate 220 x 120 mm



HM-MS3 stainless steel plate 170 x 140 mm



HM-MS4 stainless steel plate 230 x 140 mm